



Bottles, borosilicate glass, plastic coated, reagent and media, screw neck, ISO 4796, with retrace code

01

The plastic coating protects against mechanical damage and contains the contents should the glass break. The co-polymer based plastic material remains transparent and adheres to the glass surface even after repeated sterilisation in an autoclave. Steam up to 135°C; do not use distilled water for cooling. The plastic coating is largely UV absorbent to 380nm so the bottles can be used in a similar way to amber bottles. Graduated without cap or pouring ring. Do not autoclave bottles with a tightly screwed cap.
For caps and pouring rings, see page 170.

<http://schott.com/labware/english/products/duran/certification/batch-certificate.htm>

Catalogue No	Alt. No	Capacity, mL	ISO thread GL	Height, mm	O.D., mm	Pack qty
BTF-685-031K	1092676	25	25	70	36	10
BTF-685-051E	1092677	50	32	87	46	10
BTF-685-071V	2180524	100	45	100	56	10
BTF-685-091P	2180536	250	45	138	70	10
BTF-685-111M	2180544	500	45	176	86	10
BTF-685-130Y	2180554	1,000	45	225	101	1
BTF-685-150C	2180563	2,000	45	262	136	1
BTF-685-170T	2180573	5,000	45	335	186	1



Bottles, square, borosilicate, reagent and media, screw neck, DURAN®, with retrace code

01

With all the properties of the DURAN® round bottles, plus the additional benefit of saving space. Using a square bottle can save up to 20.3% in space. Supplied with polypropylene caps and pouring rings.
For spare caps and pouring rings, see page 170.

<http://schott.com/labware/english/products/duran/certification/batch-certificate.htm>

Catalogue No	Alt. No	Capacity, mL	ISO thread GL	Height, mm	O.D., mm	Pack qty
BTF-710-010U	21820245	100	32	109	50	10
BTF-710-020R	21820365	250	45	143	64	10
BTF-710-030X	21820445	500	45	181	78	10
BTF-710-040L	21820545	1,000	45	222	94	10